

印字表

NP1X3206-W NP1X3202-W		
GPN-FU2Y/GPN-FU2T GPP-FU2RY/GPP-FU2RT		
0.0	20 20	1.0
0.1	19 19	1.1
0.2	18 18	1.2
0.3	17 17	1.3
0.4	16 16	1.4
0.5	15 15	1.5
0.6	14 14	1.6
0.7	13 13	1.7
0.8	12 12	1.8
0.9	11 11	1.9
0.10	10 10	1.10
0.11	9 9	1.11
0.12	8 8	1.12
0.13	7 7	1.13
0.14	6 6	1.14
0.15	5 5	1.15
	4 4	
	3 3	
CO, B	2 2	
CO, A	1 1	

FCN插针40芯

NP1X3206-A		
GPN-FU3Y/GPN-FU3T GPP-FU3RY/GPP-FU3RT		
PORT9 (1.8)	20 20	PORT21 (2.4)
PORT10 (1.9)	19 19	PORT22 (2.5)
PORT11 (1.10)	18 18	PORT23 (2.6)
PORT12 (1.11)	17 17	PORT24 (2.7)
PORT13 (1.12)	16 16	PORT25 (2.8)
PORT14 (1.13)	15 15	PORT26 (2.9)
PORT15 (1.14)	14 14	PORT27 (2.10)
PORT16 (1.15)	13 13	PORT28 (2.11)
PORT17 (2.0)	12 12	PORT29 (2.12)
PORT18 (2.1)	11 11	PORT30 (2.13)
PORT19 (2.2)	10 10	PORT31 (2.14)
PORT20 (2.3)	9 9	PORT32 (2.15)
CO, B4	8 8	CO, A4
CO, B3	7 7	CO, A3
PORT1 (1.0)	6 6	PORT5 (1.4)
CO, B2	5 5	CO, A2
PORT2 (1.1)	4 4	PORT6 (1.5)
PORT3 (1.2)	3 3	PORT7 (1.6)
CO, B1	2 2	CO, A1
PORT4 (1.3)	1 1	PORT8 (1.7)

FCN插针40芯

NP1X6406-W		
GPN-FU4Y/GPN-FU4T GPP-FU4RY/GPP-FU4RT		
0.0	20 20	1.0
0.1	19 19	1.1
0.2	18 18	1.2
0.3	17 17	1.3
0.4	16 16	1.4
0.5	15 15	1.5
0.6	14 14	1.6
0.7	13 13	1.7
0.8	12 12	1.8
0.9	11 11	1.9
0.10	10 10	1.10
0.11	9 9	1.11
0.12	8 8	1.12
0.13	7 7	1.13
0.14	6 6	1.14
0.15	5 5	1.15
	4 4	
	3 3	
CO, B	2 2	
CO, A	1 1	

FCN插针40芯

GPN-FU5Y/GPN-FU5T GPP-FU5RY/GPP-FU5RT		
2.0	20 20	3.0
2.1	19 19	3.1
2.2	18 18	3.2
2.3	17 17	3.3
2.4	16 16	3.4
2.5	15 15	3.5
2.6	14 14	3.6
2.7	13 13	3.7
2.8	12 12	3.8
2.9	11 11	3.9
2.10	10 10	3.10
2.11	9 9	3.11
2.12	8 8	3.12
2.13	7 7	3.13
2.14	6 6	3.14
2.15	5 5	3.15
	4 4	
	3 3	
C1, B	2 2	
C1, A	1 1	

FCN插针40芯

NP1Y32T09P1-A		
GPN-FU6Y/GPN-FU6T GPP-FU6RY/GPP-FU6RT		
PORT9 (12.8)	20 20	PORT21 (13.4)
PORT10 (12.9)	19 19	PORT22 (13.5)
PORT11 (12.10)	18 18	PORT23 (13.6)
PORT12 (12.11)	17 17	PORT24 (13.7)
PORT13 (12.12)	16 16	PORT25 (13.8)
PORT14 (12.13)	15 15	PORT26 (13.9)
PORT15 (12.14)	14 14	PORT27 (13.10)
PORT16 (12.15)	13 13	PORT28 (13.11)
PORT17 (13.0)	12 12	PORT29 (13.12)
PORT18 (13.1)	11 11	PORT30 (13.13)
PORT19 (13.2)	10 10	PORT31 (13.14)
PORT20 (13.3)	9 9	PORT32 (13.15)
P, B4	8 8	P, A4
P, B3	7 7	P, A3
PORT1 (12.0)	6 6	PORT5 (12.4)
M, B2	5 5	M, A2
PORT2 (12.1)	4 4	PORT6 (12.5)
PORT3 (12.2)	3 3	PORT7 (12.6)
M, B1	2 2	M, A1
PORT4 (12.3)	1 1	PORT8 (12.7)

FCN插针40芯

NP1Y32T09P1 NP1Y32U09P1		
GPN-FU7Y/GPN-FU7T GPP-FU7RY/GPP-FU7RT		
0.0	20 20	1.0
0.1	19 19	1.1
0.2	18 18	1.2
0.3	17 17	1.3
0.4	16 16	1.4
0.5	15 15	1.5
0.6	14 14	1.6
0.7	13 13	1.7
0.8	12 12	1.8
0.9	11 11	1.9
0.10	10 10	1.10
0.11	9 9	1.11
0.12	8 8	1.12
0.13	7 7	1.13
0.14	6 6	1.14
0.15	5 5	1.15
	4 4	
	3 3	
PO, B	2 2	MO, B
PO, A	1 1	MO, A

FCN插针40芯

NP1Y64T09P1 NP1Y64U09P1		
GPN-FU8Y/GPN-FU8T GPP-FU8RY/GPP-FU8RT		
0.0	20 20	1.0
0.1	19 19	1.1
0.2	18 18	1.2
0.3	17 17	1.3
0.4	16 16	1.4
0.5	15 15	1.5
0.6	14 14	1.6
0.7	13 13	1.7
0.8	12 12	1.8
0.9	11 11	1.9
0.10	10 10	1.10
0.11	9 9	1.11
0.12	8 8	1.12
0.13	7 7	1.13
0.14	6 6	1.14
0.15	5 5	1.15
	4 4	
	3 3	
PO, B	2 2	MO, B
PO, A	1 1	MO, A

FCN插针40芯

GPN-FU9Y/GPN-FU9T GPP-FU9RY/GPP-FU9RT		
2.0	20 20	3.0
2.1	19 19	3.1
2.2	18 18	3.2
2.3	17 17	3.3
2.4	16 16	3.4
2.5	15 15	3.5
2.6	14 14	3.6
2.7	13 13	3.7
2.8	12 12	3.8
2.9	11 11	3.9
2.10	10 10	3.10
2.11	9 9	3.11
2.12	8 8	3.12
2.13	7 7	3.13
2.14	6 6	3.14
2.15	5 5	3.15
	4 4	
	3 3	
P1, B	2 2	M1, B
P1, A	1 1	M1, A

FCN插针40芯

NP1W3206T NP1W3206U		
GPN-FU10Y/GPN-FU10T GPP-FU10RY/GPP-FU10RT		
0.0	20 20	1.0
0.1	19 19	1.1
0.2	18 18	1.2
0.3	17 17	1.3
0.4	16 16	1.4
0.5	15 15	1.5
0.6	14 14	1.6
0.7	13 13	1.7
0.8	12 12	1.8
0.9	11 11	1.9
0.10	10 10	1.10
0.11	9 9	1.11
0.12	8 8	1.12
0.13	7 7	1.13
0.14	6 6	1.14
0.15	5 5	1.15
	4 4	
	3 3	
	2 2	PO
	1 1	MO

FCN插针40芯

NP1F-HC2、NP1F-HC2MR NP1F-HC2MR1		
GPN-FU13Y/GPN-FU13T GPP-FU13RY/GPP-FU13RT		
B20	20 20	A20
B19	19 19	A19
B18	18 18	A18
B17	17 17	A17
B16	16 16	A16
B15	15 15	A15
B14	14 14	A14
B13	13 13	A13
B12	12 12	A12
B11	11 11	A11
B10	10 10	A10
B9	9 9	A9
B8	8 8	A8
B7	7 7	A7
B6	6 6	A6
B5	5 5	A5
B4	4 4	A4
B3	3 3	A3
B2	2 2	A2
B1	1 1	A1

FCN插针40芯

\*由于此处的产品信号名较复杂，所以套号码管上刻印了连接器针No.。

NP1W6406T NP1W6406U		
GPN-FU11Y/GPN-FU11T GPP-FU11RY/GPP-FU11RT		
0.0	20 20	1.0
0.1	19 19	1.1
0.2	18 18	1.2
0.3	17 17	1.3
0.4	16 16	1.4
0.5	15 15	1.5
0.6	14 14	1.6
0.7	13 13	1.7
0.8	12 12	1.8
0.9	11 11	1.9
0.10	10 10	1.10
0.11	9 9	1.11
0.12	8 8	1.12
0.13	7 7	1.13
0.14	6 6	1.14
0.15	5 5	1.15
	4 4	
	3 3	
CO, B	2 2	
CO, A	1 1	

FCN插针40芯

GPN-FU12Y/GPN-FU12T GPP-FU12RY/GPP-FU12RT		
2.0	20 20	3.0
2.1	19 19	3.1
2.2	18 18	3.2
2.3	17 17	3.3
2.4	16 16	3.4
2.5	15 15	3.5
2.6	14 14	3.6
2.7	13 13	3.7
2.8	12 12	3.8
2.9	11 11	3.9
2.10	10 10	3.10
2.11	9 9	3.11
2.12	8 8	3.12
2.13	7 7	3.13
2.14	6 6	3.14
2.15	5 5	3.15
	4 4	
	3 3	
P1, B	2 2	M1, B
P1, A	1 1	M1, A

FCN插针40芯

\*为区别相同的信号名，此处的信号名可能与PLC制造商的使用手册中的记载有少许差异，请确认后再订购。  
\*无信号名标记的引脚为未接线。

产品目录  
交易指南

继电器

开关按钮·开关盒·  
指示灯·蜂鸣器  
多层信号灯·  
旋转报警灯

LED灯

开关电源·  
噪音滤波器·变压器

电路保护器·  
保险丝

测量仪表

AC/DC风扇

连接器线束

机器设备线束

测量通信线束

LAN线缆·  
光纤

连接器

压着端子·  
测试用端子

端子台

电缆

保护管·软管·  
线槽

固定部件

AC电源线·  
接插件

电源排插

配线工具

箱体

检测探头·  
镜头·附件

显示器·显  
示器支架

扩展卡

键盘·鼠标·  
周边产品

技术资料  
索引