

深溝玉軸受 一両シールド形
深沟滚珠轴承
 一 双盖式 一

大订单
 对应
BIG ORDER

库存品
 最快当天发货

CAD数据文件夹名: 13_Bearings_with_Holder

① 为米思米品质产品。也可用于需要高负载、高转速、高旋转精度的场合。同一产品的中精度零件请参阅右页

Order 订货范例 **型式** **B6901ZZ**

B6□□□ZZ

CAD 2D 3D 库存 RoHS 10

材质 SUJ2
 轴承精度 GB 307 PO
 JIS B 1514 0级

型式	d	D	B	r (min.)	基本额定负载		容许转速 rpm (参考)	安装尺寸				重量 (g) (参考)
					Cr (动) kN	Cor (静) kN		Ds		R		
								(min.)	(max.)	(max.)	(max.)	
B6700ZZ	10	15	4	0.2	0.85	0.43	15000	10.4	11.21	14.2	0.2	2
B6800ZZ		19	5		1.83	0.925	34000		12.5	17		5
B6900ZZ		22	6	0.3	2.70	1.27	32000	12	13	20	0.3	9
B6000ZZ		26	8		4.55	1.96	30000		13.5	24		19
B6200ZZ		30	9		5.10	2.39	24000		16	26		32
B6300ZZ		35	11	0.6	8.1	3.45	21000	14	16.5	31	0.6	52
B6701ZZ	12	18	4	0.2	0.92	0.53	13000	12.4	13.86	16.7	0.2	3
B6801ZZ		21	5		1.92	1.04	32000		14.5	19		6
B6901ZZ		24	6	0.3	2.89	1.46	30000	14	15	22	0.3	11
B6001ZZ		28	8		5.10	2.39	27000		16	26		21
B6201ZZ		32	10	0.6	6.10	2.75	22000	16	17	28	0.6	37
B6301ZZ		37	12	1	9.7	4.2	19000	17	18	32	1.0	60
B6702ZZ	15	21	4	0.2	0.93	0.58	11000	15.4	16.86	19.7	0.2	4
B6802ZZ		24	5		2.08	1.26	27000		17.5	22		7
B6902ZZ		28	7	0.3	3.65	2.00	26000	17	17.5	26	0.3	16
B6002ZZ		32	9		5.60	2.83	23000		19	30		30
B6202ZZ		35	11	0.6	7.75	3.60	19000	19	20	31	0.6	45
B6302ZZ		42	13	1	11.4	5.45	17000	20	22.5	37	1.0	83
B6703ZZ	17	23	4	0.2	1.0	0.65	9500	17.4	18.86	21.1	0.2	4
B6803ZZ		26	5		2.23	1.46	25000		19.5	24		8
B6903ZZ		30	7	0.3	4.65	2.58	23000	19	20	28	0.3	18
B6003ZZ		35	10		6.80	3.35	20000		21	33		39
B6203ZZ		40	12	0.6	9.60	4.60	17000	21	23	36	0.6	66
B6303ZZ		47	14	1	13.6	6.65	15000	22	25.5	42	1.0	113
B6704ZZ	20	27	4	0.2	1.40	0.72	8500	20.4	22.36	25.5	0.2	6
B6804ZZ		32	7		4.00	2.47	20000		22.5	30		19
B6904ZZ		37	9	0.3	6.40	3.70	19000	22	24	35	0.3	36
B6004ZZ		42	12	0.6	9.40	5.05	17000	24	26	38	0.6	69
B6204ZZ		47	14	1.0	12.80	6.65	14000	25	28	42	1.0	106
B6304ZZ		52	15	1.1	15.9	7.9	13000	26.5	28	45.5	1.0	145
B6805ZZ	25	37	7	0.3	4.30	2.95	18000		35			22
B6905ZZ		42	9		7.05	4.55	16000	27	29	40	0.3	42
B6005ZZ		47	12	0.6	10.10	5.85	15000	29	30.5	43	0.6	80
B6205ZZ		52	15	1.0	14.00	7.85	12000	30	32	47	1.0	128
B6305ZZ		62	17	1.1	20.6	11.2	11000	31.5	36	55.5	1.0	235
B6806ZZ		42	7		4.70	3.65	15000		33	40		26
B6906ZZ	30	47	9	0.3	7.25	5.00	14000	32	34	45	0.3	48
B6006ZZ		55	13		13.20	8.30	12000		37	50		116
B6206ZZ		62	16	1.0	19.50	11.30	10000	35	39	57	1.0	199
B6306ZZ		72	19	1.1	26.7	15	9200	36.5	42.5	65.5	1.0	345
B6807ZZ		47	7	0.3	4.90	4.05	13000	37	38	45	0.3	29
B6907ZZ		55	10	0.6	9.55	6.85	12000	39	40	51	0.6	74
B6007ZZ	35	62	14	1.0	16.00	10.30	11000	40	42	57	1.0	155
B6207ZZ		72	17	1.1	25.70	15.30	9000	41.5	45	65.5	1.0	288
B6307ZZ		80	21	1.5	33.5	19.2	8400	43	47	72	1.5	469
B6808ZZ		52	7	0.3	5.10	4.40	12000	42	43	50	0.3	33
B6908ZZ		62	12	0.6	12.20	8.90	11000	44	45	58	0.6	110
B6008ZZ		68	15	1.0	16.80	11.50	9500	45	47	63		190
B6208ZZ	40	80	18	1.1	29.10	17.80	8200	46.5	51	73.5	1.0	366
B6308ZZ		90	23	1.5	40.5	24	7500	48	53	82	1.5	636
B6809ZZ		58	7	0.3	6.18	5.38	11000	47	47.5	56	0.3	38
B6909ZZ		68	12	0.6	14.1	10.8	9500	49	50	64	0.6	126
B6009ZZ		75	16	1	20.9	15.2	8800	50	53.5	70	1.0	241
B6209ZZ		85	19	1.1	31.5	20.4	7500	51.5	55.5	78.5	1.5	429
B6309ZZ	45	100	25	1.5	53	32	6700	53	61.5	92	1.5	820
B6810ZZ		65	7	0.3	6.6	6.09	9500	52	52.5	63	0.3	50
B6910ZZ		72	12	0.6	14.5	11.7	9000	54	55	68	0.6	135
B6010ZZ		80	16	1.0	21.80	16.60	8300	55.0	57.5	75.0	1.0	261
B6210ZZ		90	20	1.1	35.00	23.20	7000	56.5	60.0	83.5	1.0	454
B6310ZZ		110	27	2	62.0	38	6000	59	68	101	2	1006

① 米思米不承诺此产品品牌。

Delivery 交货期 **库存品**

① 隔日上海·广州发货 P.9
 (17:00前订购的库存品可当日发货。)

数量分类	标准订购	特殊订购
	小单	大单
数量	1~100	101~
交货期	通常	另行报价

① 超过表中标示的数量时, 请在WOS中确认。 P.9

