


RING TERMINALS

Material

Insulation: Vinyl
Terminal Body: Copper
Plating: Tin



WIRE RANGE	STUD SIZE		ITEM NO.	DIMENSION mm(inch)								COLOR	STANDARD	TOOLS	Q'TY BOX	
mm² (A.W.G.)	Metric	American		d2	W	F	L	E	D	d1	T					
0.5-1.5 (22-16)	3	#4	RV1-3.2	3.2 (.126)	5.5 (.216)	5.0 (.197)	17.5 (.689)	10.0 (.394)	4.0 (.157)	1.7 (.067)	0.75(.030)	Red	 	K.S. MODEL KST2000A HRI-126 WITH DIE INDEX COLOR: RED OR IZUMI MODEL 34 WITH DIE INDEX COLOR: RED	1,000	
	3.5	#6	RVS1-3.7	3.7 (.146)											1,000	
	3.5	#6	RVM1-3.7	3.7 (.146)	6.6 (.260)	6.3 (.248)	19.4 (.764)								1,000	
	3.5	#6	RVL1-3.7	3.7 (.146)	8.0 (.315)	7.0 (.276)	20.8 (.819)								1,000	
	4	#8	RVS1-4	4.3 (.169)	6.6 (.260)	6.3 (.248)	19.4 (.764)								1,000	
	4	#8	RVL1-4	4.3 (.169)	8.0 (.315)	7.0 (.276)	20.8 (.819)								1,000	
	5	#10	RV1-5	5.3 (.209)											1,000	
	5	#10	RVL1-5	5.3 (.209)	11.6 (.457)	11.0 (.433)	26.8(1.055)								1,000	
	6	1/4"	RV1-6	6.4 (.252)											1,000	
	8	5/16"	RV1-8	8.4 (.331)											1,000	
	10	3/8"	RV1-10	10.5 (.413)	13.6 (.535)	13.9 (.547)	30.5(1.201)								1,000	
	12	1/2"	RV1-12	13.0 (.512)	19.2 (.756)	16.0 (.630)	35.4(1.394)								1,000	
	14	9/16"	RV1-14	15.0 (.591)	27.0(1.063)	21.0 (.827)	44.3(1.744)				0.8 (.031)				1,000	
16	5/8"	RV1-16	17.0 (.669)	1,000												
20	3/4"	RV1-20	21.0 (.827)	1,000												
1.5-2.5 (16-14)	3	#4	RV2-3.2	3.2 (.126)	6.6 (.260)	4.8 (.189)	17.8 (.701)	10.0 (.394)	4.5 (.177)	2.3 (.091)	0.8 (.031)	Blue	 	K.S. MODEL KST2000A HRI-126 WITH DIE INDEX COLOR: BLUE OR IZUMI MODEL 34 WITH DIE INDEX COLOR: BLUE	1,000	
	3.5	#6	RVS2-3.7	3.7 (.146)		6.3 (.248)	19.4 (.764)								1,000	
	3.5	#6	RVM2-3.7	3.7 (.146)											1,000	
	3.5	#6	RVL2-3.7	3.7 (.146)	8.5 (.335)	7.4 (.291)	21.8 (.858)								1,000	
	4	#8	RVS2-4	4.3 (.169)	6.6 (.260)	6.3 (.248)	19.4 (.764)								1,000	
	4	#8	RVL2-4	4.3 (.169)	8.5 (.335)	7.8 (.307)	21.8 (.858)								1,000	
	5	#10	RVS2-5	5.3 (.209)											1,000	
	5	#10	RVL2-5	5.3 (.209)	9.5 (.374)	7.3 (.287)	1,000									
	6	1/4"	RV2-6	6.4 (.252)	12.0 (.472)	11.0 (.433)	26.8(1.055)								1,000	