

35224

動向鋼珠螺絲 SWIVEL CLAMPING SCREW


- 材質:本體SCM21，鋼珠SUJ2
- 硬度:本體HRC28~32°，鋼珠HR62°
- 表面染黑處理。
- 配合治具零件的組成，可做夾持或支持用，點接觸，工件不易變形。
- Material:Bolt-SCM21,Ball-SUJ2.
- Hardness:Bolt-HRC28~32° ,Ball-HR62° .
- Surface treatment:Black Oxide.
- Ideal for clamping odd shaped work pieces.
Less chance of deforming the work piece due the rounded tip.

單位:mm


訂購編號 Order No.	型號 Model	A	B	C	max (KN)	重量(g) Weight
35224-02	PT16A-0615	13.5	M6	3	9	2.4
35224-04	PT16A-0625	23.5	M6	3	9	3.8
35224-06	PT16A-0812	12	M8	4	15	3.2
35224-08	PT16A-0820	20	M8	4	15	5.8
35224-10	PT16A-0830	30	M8	4	15	9
35224-12	PT16A-1015	17	M10	5	20	6.7
35224-14	PT16A-1025	27	M10	5	20	11.2
35224-16	PT16A-1035	37	M10	5	20	16.2
35224-18	PT16A-1220	23.2	M12	6	30	12.5
35224-20	PT16A-1230	31.2	M12	6	30	20
35224-22	PT16A-1240	41.2	M12	6	30	30
35224-24	PT16A-1250	51.2	M12	6	30	40
35224-26	PT16A-1625	25.6	M16	8	60	28
35224-28	PT16A-1635	35.6	M16	8	60	40
35224-30	PT16A-1645	45.6	M16	8	60	45
35224-32	PT16A-1655	55.6	M16	8	60	55
35224-34	PT16A-1665	65.6	M16	8	60	65




● PT16A
圓球面 ROUND END



● PT16B
平面 FLATD END



● PT16C
齒面 SERRATED END



單位:mm

訂購編號 Order No.	型號 Model	A	B	C	max (KN)	重量(g) Weight
35224-36	PT16B-0615	13	M6	3	9	2.4
35224-38	PT16B-0625	23	M6	3	9	3.8
35224-40	PT16B-0812	11.2	M8	4	15	3.2
35224-42	PT16B-0820	19.2	M8	4	15	5.8
35224-44	PT16B-0830	29.2	M8	4	15	9
35224-46	PT16B-1015	15	M10	5	20	6.7
35224-48	PT16B-1025	25	M10	5	20	11.2
35224-50	PT16B-1035	35	M10	5	20	16.2
35224-52	PT16B-1220	22	M12	6	30	12.5
35224-54	PT16B-1230	30	M12	6	30	20
35224-56	PT16B-1240	40	M12	6	30	30
35224-58	PT16B-1250	50	M12	6	30	40
35224-60	PT16B-1625	24	M16	8	60	28
35224-62	PT16B-1635	34	M16	8	60	40
35224-64	PT16B-1645	44	M16	8	60	45
35224-66	PT16B-1655	54	M16	8	60	55
35224-68	PT16B-1665	64	M16	8	60	65

單位:mm

訂購編號 Order No.	型號 Model	A	B	C	max (KN)	重量(g) Weight
35224-70	PT16C-0615	13	M6	3	9	2.4
35224-72	PT16C-0625	23	M6	3	9	3.8
35224-74	PT16C-0812	11.2	M8	4	15	3.2
35224-76	PT16C-0820	19.2	M8	4	15	5.8
35224-78	PT16C-0830	29.2	M8	4	15	9
35224-80	PT16C-1015	15	M10	5	20	6.7
35224-82	PT16C-1025	25	M10	5	20	11.2
35224-84	PT16C-1035	35	M10	5	20	16.2
35224-86	PT16C-1220	22	M12	6	30	12.5
35224-88	PT16C-1230	30	M12	6	30	20
35224-90	PT16C-1240	40	M12	6	30	30
35224-91	PT16C-1250	50	M12	6	30	40
35224-92	PT16C-1625	24	M16	8	60	28
35224-93	PT16C-1635	34	M16	8	60	40
35224-94	PT16C-1645	44	M16	8	60	45
35224-95	PT16C-1655	54	M16	8	60	55
35224-96	PT16C-1665	64	M16	8	60	65