


ZZ-002786 ZM-C型精密钻头磨刀机

PRECISION DRILL RE-SHARPENING MACHINE

- 产品特点：精巧、容易、快速、安全，一次装夹，可精确地磨削钻头的切削刃、横刃。
- 采用CBN砂轮，不需要校准或修复，能够对高速钢、硬质合金等钻头进行精密磨削。
- Feature: easy operate, quickly, safe. Once hold will finish cutting edge and crossing edge.
- Suitable to precisely grind HSS, carbide-point drill with CBN grinding wheel.



ZM-C13A




ZM-C26A

订单号 Order No.	磨削直径范围 Range of Grinding Dia	磨削锥角范围 Range of Grinding Taper	磨量调节范围 Adjust Range	配备夹头 Equipped Collets	电机 Motor
ZM-C13A	φ 3—φ 13	118°—135°	≤1mm	ER20	220V/120W/7000rpm
ZM-C26A	φ 13—φ 26	100°—140°	≤1mm	ER40	220V/200W/4200rpm

ZZ-002788 ZM-C13C型精密钻头磨刀机

PRECISION DRILL RE-SHARPENING MACHINE



订单号 Order No.	磨削直径范围 Range of Grinding Dia	磨削锥角范围 Range of Grinding Taper	磨量调节范围 Adjust Range	配备夹头 Equipped Collets	电机 Motor
ZM-C13C	φ 3—φ 13	90°—140°	≤1mm	ER20	220V/120W/7000rpm

该磨刀机采用立方氮化硼 (CBN) 和金刚石 (RVD) 两种砂轮，不需要校准或修复，能够对高速钢、硬质合金等钻头进行精密磨削，高速钢钻头采用CBN砂轮，硬质合金钻头采用RVD砂轮。

CBN wheel is suitable to precisely grind HSS drill and diamond wheel for carbide drill.